

HE HITECH
MILANO **EUROPE**

METALLOGRAPHIC SAMPLE PREPARATION



P4K DISPENSER

**PULITRICI
POLISHERS**

2021

REV. 00.03.25

P4K DISPENSER

AP312KA



Schermata iniziale
Home



Menu



Settaggio parametri
Parameters setting



Funzionamento pompe
Pumps operation display



Tramite l'elettronica a touch screen di facile e intuitivo utilizzo è possibile programmare il dosaggio sia come numero di impulsi al minuto sia come durata degli stessi. Il distributore di fluidi P4K può essere abbinato a tutte le pulitrici di qualsiasi marca e supportare il processo di lucidatura indipendentemente. Il dispensatore P4K può essere anche collegato alle pulitrici Hitech Europe serie AP312KA, sfruttando lo start/stop delle stesse.

Through the easy to use touch-screen monitor you can regulate the quantity of fluids by setting the desired amount of pulses per minute and the duration of each pulse. The P4K dispenser can be paired to any polisher and can single handedly support the polishing process.

The P4K dispenser, when paired with a Hitech Europe AP312KA series polisher, can be operated directly through the polisher touch-screen.

DATI TECNICI / SPECIFICATIONS

- Touch screen a colori da 7"
- 4 pompe peristaltiche programmabili
- Braccio telescopico orientabile
- 4 flaconi per fluidi
- Cover in materiale plastico antiurto
- Alimentazione 230V 50 Hz
- Dimensioni macchina 500x200x350
- Peso 7 kg
- 7" color touch-screen
- 4 programmable peristaltic pumps
- Adjustable telescopic arm
- No. 4 bottles for fluid
- Shockproof resin cover
- Power supply 230V 50 Hz
- Dimensions 500x200x350
- Weight 7 kg